

SSB-105-108JA/B



Supplier/ wholesaler/ manufacturer of 4"(105mm) diamond cutting blades /saw blades / circular blades for tile / Marble / Microlite



=Min Order Quantity: 500 Pieces
Supply Ability: 300,000 Pieces per month
Payment Terms: T/T,L/C
Price: To be negotiated

[Send email to us](#)

[Download To PDF](#)

Product Detail

Product Tags

Net Weight(g)	59g
Numbers of Teeth	108T
Teeth Height	10mm
Blade Diameter	4"(105mm)
Disc Bore Size	4/5"(20mm)
Blade Thickness	1.2mm
MAX.RPM	12000
Cutting Condition	Dry/Wet

High quality 4"(105mm) diamond saw blade for tile , marble and microlite with unique composition and high working performance. design independently developed by our team and the unique segment design, we can improve the cutting efficiency and maximize the cutting efficiency.



The contact area decreases and the heat dissipation is accelerated. The friction is also reduced. In the same environment, our products are sharper and faster than general saw blades. It can bring the best cutting effect.

Our diamond saw blade series can be used with power machinery and have different appearance which award design patent certificate for your choice.

On quality our products can adjust to different markets. Besides, the unique segment design improved and maximized the cutting speed and efficiency. In the same condition, our blades are sharper and faster than the ordinary blades.

However, the life of the saw blade is affected by different terrains and cutting objects, we will adjust the product formula for different areas to ensure the cutting efficiency.

We will make sample specially according to clients' request , and the sample cost and freight charge will be paid by clients, but the sample cost will be return back to client after order confirmed in future. And we also support OEM and ODM designs. Besides, 24H/7D after sale services is available.

High cost performance is always our aim. We hope that we would have more partners in the future and make more contributions to the diamond tools industry's development together. Welcome to inquiry.

Advantage:

1. Our company is a manufacturer, so the price must be the best for you.
2. We have full-automatic machine to produce product , it can make our quality steady and safety.
3. Using the patented teeth independently developed by our team, the design of the cutter head VOV improves the cutting efficiency, and the unique cutter head design maximizes the efficiency

Percentage of raw materials :

- High quality carbon structural steel matrix
- 65 manganese steel
- High grade diamond
- Intermediate or above quality
- Homemade alloy powder.

Application:

- High cutting accuracy,
- Fine grain particles,

- Ceramics, microspar, marble,
- Glass brick.

Tool Compatibility

- Stone cutting machine (marble machine)
- Angle grinder
- Bench cutting machine
- Wall slot machine is the main

Using machine



Safety and working instructions

- Safety and working instructions for using diamond cutting pieces
- When installing or replacing the cutting piece, unplug the plug from the socket.
- Please choose the appropriate cutting piece according to the material to be processed.
- Cleaning flanges, shafts and cutting pieces.
- The flange shall be at least 1 / 3 of the diameter of the cutting piece
- The diameter of the shaft must be as large as the hole in the cutting piece.
- Do not privately increase the hole in the cutting piece.
- The direction of the arrow on the cutting piece and the steering of the machine must be caused by the direction of the arrow on the cutting piece and the steering of the machine.
- The maximum speed of the machine shall not be higher than the allowable maximum speed of the cutting piece.
- Can only do right angle or straight line cutting, engaging in curved angle cutting may cause section core fracture or section fracture.
- Avoid pressing the machine and hitting the material with the machine. Don't let the cutting piece overheat. Stop working at the right time to cool the cutting piece.
- Please remove the cutting piece when transporting the machine to avoid unnecessary damage.
- Wear protective goggles, industrial gloves, masks, safety shoes and work clothes when working.
- Protective cover, guide plate and vacuum must be used when working
- When doing wet cutting, isolation transformer must be used, and there must be a strong non-grounding socket on the isolation transformer.

FAQ

Q:Are samples available for quality test?

A: Yes, free samples can be prepared for quality test,and we bear the freight charges.

Q: Do you accept OEM Brand?

A: Yes,OEM Brand is accepted.We can also design label for you for free.

Q: Do you have any certificate?

A: Yes, we have MPA,ISO certificates .

Q:How could you ensure the quality?

A:Only high quality and stable batch products can ensure user's safety and consistent effect.To ensure this, all our products will pass the semi-product testing, finished- product testing and inspection before delivering.Quality passes only after 3 times testing.