

SSB-105-YA/B



Supplier / wholesaler/ wholesaler of 4"(105mm) diamond cutting blades / circular saw blades for wall groove /granite



Min Order Quantity: 500 Pieces
Supply Ability: 300,000 Pieces per month
Payment Terms: T/T,L/C
Price: To be negotiated

[Send email to us](#)

[Download To PDF](#)

[Product Detail](#)

[Product Tags](#)

Net Weight(g)	59g
Numbers of Teeth	105T
Teeth Height	10mm
Blade Diameter	4"(105mm)
Disc Bore Size	4/5"(20mm)
Blade Thickness	1.2mm
MAX.RPM	12000
Cutting Condition	Dry/Wet

The diamond saw blade of 4"(105mm) is forged by high quality carbon structural steel matrix, 65 Mn steel, high grade diamond and self-made alloy powder, which is highly recognized by the industry.



Our cutting blades are sharper and more efficient to complete our work. At the same time, the product is

more wear-resistant, which can extend the service life of the product and save the consumption of the saw blade. So as to achieve the goal of more, faster, better and less.

This product will also be customized according to customers in different regions and construction objects. Realize the maximization of product value and the optimization of user experience.

Widely used for cutting and nondestructive grooving on marble, ceramic tile, concrete on manual cutting machine. Suitable for dry or wet cutting. However, the working performance of the product is better when working under the wet condition.

We are committed to research and development of products conducive to the market, to ensure high quality products and services, so that customers who use our products can improve work efficiency, reduce manpower and material resources, and create a good product experience for customers.

At the same time, we also pay attention to the impact of production on the natural environment, we invest in the purchase of environmental protection equipment, in production to reduce the pollution and damage to the natural environment as much as possible, and actively protect the natural environment. For example, the company will organize all employees to participate in some environmental protection public welfare activities on a regular basis.

Shipping:

Our shipping port is Tianjin port. Our delivery time is usually 10-15 days, and this is determined according to the quantity of products you need.

Quality Control:

1. Strict Raw material inspection
2. Professional formula
3. Production process control(PDCA+7S Principle)
4. Test the product repeatedly to ensure its using function
5. Products pass SGS inspection

Percentage of raw materials :

- High quality carbon structural steel matrix
- 65 manganese steel
- High grade diamond
- Intermediate or above quality
- Homemade alloy powder.

Application:

- High cutting accuracy,
- Fine grain particles,
- Ceramics, microspar, marble,
- Glass brick.

Tool Compatibility

- Stone cutting machine (marble machine)
- Angle grinder
- Bench cutting machine
- Wall slot machine is the main

Using machine



Safety and working instructions

- Safety and working instructions for using diamond cutting pieces
- When installing or replacing the cutting piece, unplug the plug from the socket.
- Please choose the appropriate cutting piece according to the material to be processed.
- Cleaning flanges, shafts and cutting pieces.
- The flange shall be at least $1/3$ of the diameter of the cutting piece
- The diameter of the shaft must be as large as the hole in the cutting piece.
- Do not privately increase the hole in the cutting piece.
- The direction of the arrow on the cutting piece and the steering of the machine must be caused by the direction of the arrow on the cutting piece and the steering of the machine.
- The maximum speed of the machine shall not be higher than the allowable maximum speed of the cutting piece.
- Can only do right angle or straight line cutting, engaging in curved angle cutting may cause section core fracture or section fracture.
- Avoid pressing the machine and hitting the material with the machine. Don't let the cutting piece overheat. Stop working at the right time to cool the cutting piece.
- Please remove the cutting piece when transporting the machine to avoid unnecessary damage.
- Wear protective goggles, industrial gloves, masks, safety shoes and work clothes when working.

- Protective cover, guide plate and vacuum must be used when working
- When doing wet cutting, isolation transformer must be used, and there must be a strong non-grounding socket on the isolation transformer.

FAQ

Q:Are samples available for quality test?

A: Yes, free samples can be prepared for quality test,and we bear the freight charges.

Q: Do you accept OEM Brand?

A: Yes,OEM Brand is accepted.We can also design label for you for free.

Q: Do you have any certificate?

A: Yes, we have MPA,ISO certificates .

Q:How could you ensure the quality?

A:Only high quality and stable batch products can ensure user's safety and consistent effect.To ensure this, all our products will pass the semi-product testing, finished- product testing and inspection before delivering.Quality passes only after 3 times testing.